

Ultima-Tig

Patented wet grinder for tungsten electrodes for TIG welding



- Environmentally friendly collection of toxic dust particles
- Precise grinding at the correct angle
- Perfect centring of the electrode
- Grinds down to 8 mm
- Minimal electrode waste

inelco
grinders
The way to grind

ULTIMA-TIG - high-quality tungsten electrode grinding

Environmentally friendly and safe

ULTIMA-TIG is the environmentally friendly wet grinder of Tungsten electrodes for TIG welding, with minimal wastage of the expensive electrodes. ULTIMA-TIG is constructed with a unique disposable container that automatically collects the toxic dust particles and ensures safe disposal.

Cost-effective in high-quality

ULTIMA-TIG's unique construction reduces the waste of expensive Tungsten electrodes and reduces the time spent on grinding, resulting in a short payback time. The variable angle adjustment and unique clamping system centres the electrode, so that the grinding is carried out in the correct longitudinal direction of the electrode. A precise angle is not only important for the quality of the welding seam; the number of re-ignitions between re-grinding is also increased.

Wet grinding

The combination of liquid for cooling and a high grinding speed of the diamond disc results in a polished and even surface of the Tungsten electrode. In addition, the cool wet grinding shortens the grinding time and prevents overheated and damaged electrodes.

Simple operation

Set the variable angle setting at the desired angle. Place the electrode in the electrode holder and tighten it in the stick-out. Insert the electrode holder, turn on the grinder and rotate the electrode holder until grinding is finished. After grinding, flatten the tip by placing the angle adjustment in the 90° position, if needed.

Grinder facts

Electrode size: Ø0.8 - 4 mm

Min. length: 15 mm standard (8 mm with special clamps)

Angles: 7.5° - 90° grinding angle (equal to 15° - 180° tip angle)

Technical specifications

Motor: 110V-50/60 Hz, 220V-50/60Hz

Motor effect: 280W

Motor speed: 8500 rpm

Grinding speed: 44 m/sec.

Standard unit includes

- Grinder complete with table, diamond disc and grinding liquid
- Electrode holder
- Electrode clamps for Ø1.6, 2.4 and 3.2 mm electrodes (clamps are available for other electrode sizes)

Accessories

- Electrode clamps for all diameters from Ø 0.8 to 4.0 mm
- Electrode clamps for grinding short electrodes down to 8 mm

"ULTIMA-TIG-S" is available for grinding tungsten electrodes up to Ø8 mm

Main features of Ultima-Tig

- Sealed grinding chamber with dust collector to protect the user
- Variable angle setting gives more flexibility
- Wet grinding prevents overheating of the electrode during grinding
- High grinding speed provides faster grinding and a smooth surface
- The electrode holder ensures centring of the tip and reduces wastage
- Less electrode wastage results in a short payback time



Precise adjustment of the electrode's stick-out.



Grinding angle from 7.5° - 90° creates accurate electrode tip angles of 15° - 180°.



Tip may be flattened by 1/10 mm per point in the 90° position.



Sealed disposable container for dust collection and disposal.

In Australia: Welding Automation
5/51 Taunton Drive, Cheltenham, VIC 3192
t:03 8516 2472 f:03 9011 6203
sales@weldingautomation.com.au
www.weldingautomation.com.au

inelco
grinders

Industrivej 3 · 9690 Fjerritslev · Denmark
Tel. +45 96 50 62 33 · Fax +45 96 50 62 32 · info@inelco-grinders.com
www.inelco-grinders.com